



## Journeyman™ Side-Cutters, 8-Inch



These high-leverage side cutters provide 46-Percent more cutting and gripping power than other pliers. Dual-material Journeyman handles provide a better grip without sacrificing tool strength and durability. Hot-riveted joint ensures smooth action and no handle wobble. Induction hardened cutting knives for long life.

### Specifications

<b>Type:</b>	Side Cutting Pliers	<b>Overall Length:</b>	8.89" (22.6 cm)
<b>Material:</b>	Steel	<b>Nose Type:</b>	New England
<b>Jaw Length:</b>	1.441" (3.7 cm)	<b>Jaw Width:</b>	1.209" (3.1 cm)
<b>Jaw Thickness:</b>	0.613" (1.6 cm)	<b>Jaw Capacity:</b>	1.625" (4.1 cm)
<b>Knife Length:</b>	0.719" (1.8 cm)	<b>Cut Style:</b>	Flush
<b>Joint Type:</b>	Adjustable	<b>Handle Color:</b>	Dark Blue/Black
<b>Handle Finish:</b>	Journeyman™ Dual-Material	<b>Handle Length:</b>	6.25" (15.9 cm)
<b>Insulated:</b>	No	<b>Tether Capable:</b>	No
<b>Weight:</b>	15.5 oz (440 g)		