



HIGH DENSITY CAN LINERS













High Density liners are great for paper and light-weight trash. They are a great choice for office and restroom waste, shredded paper and public areas as long as no sharp or irregularly shaped objects are being discarded.

High Density bags can easily be identified by their crinkly feel. Because they use less plastic, high density bags are generally less expensive than their low density cousins, providing a cost-effective solution. Lighter construction means lower freight, storage, and warehousing costs.

High Density can liners are temperature resistant from -40 to 212 degrees Fahrenheit. They are most often measured in microns, which is one thousandth (.001) of a millimeter. All of our clear high density liners are made with materials that are FDA approved for food storage and handling.



Can/Liner Compatibility Chart

4 Gallon  5XL44	7 Gallon  5XL45	7-10 Gallon  4KN28 1CF86	10-15 Gallon  4KN29 5XL46	20-30 Gallon  5XL47 3U870 4KN31 3CCT7	33 Gallon  4KN32 4KN33
38 Gallon  2U384	40-45 Gallon  4KN38 4KN39 4KN40 5XL50 5BB54	44 Gallon  5XL48	55 Gallon  4KN34 4KN35 4YPC4	56 Gallon  4KN42 5XL51	60 Gallon  4KN36 4KN37 5XL49 4CU29

(See reverse for product specifics)

Call or visit your local branch or go to grainger.com/toughguy for complete product line information.

©2019 W.W. Grainger, Inc. W-BUPX115-01



GRAINGER.COM® | 1.800.GRAINGER



High Density on Coreless Rolls

ITEM NUMBER	GALLON CAPACITY	SIZE	GAUGE MILS	MAX LOAD	COLOR	CASE PACK	LINERS/ROLL	ROLLS/CASE
5XL44	4	17 x 18	6	15	Clear	2000	50	40
5XL45	7	20 x 22	6	15	Clear	2000	50	40
4KN28	7-10	24 x 24	6	15	Clear	1000	50	20
1CF86	7-10	24 x 24	8	20	Clear	1000	50	20
4KN29	10-15	24 x 33	6	15	Clear	1000	50	20
5XL46	10-15	24 x 33	8	20	Clear	1000	50	20
3U870	20-30	30 x 37	10	30	Clear	500	25	20
4KN31	20-30	30 x 37	12	45	Clear	500	25	20
3CCT7	20-30	30 x 37	16	75	Clear	250	25	10
5XL47	20-30	30 x 37	8	20	Clear	500	25	20
4KN32	33	33 x 40	12	45	Clear	250	25	10
4KN33	33	33 x 40	16	75	Clear	250	25	10
2U384	38	30 x 49	17	80	Black	250	25	10
5XL48	44	37 x 46	14	55	Clear	250	25	10
4KN38	40-45	40 x 48	10	30	Clear	250	25	10
4KN39	40-45	40 x 48	12	45	Clear	250	25	10
4KN40	40-45	40 x 48	16	75	Clear	250	25	10
5XL50	40-45	40 x 48	22	85	Black	150	15	10
5BB54	40-45	40 x 48	22	85	Clear	150	15	10
4KN34	55	36 x 60	12	45	Clear	200	25	8
4KN35	55	36 x 60	16	75	Clear	200	25	8
4YPC4	55 Brute	41 x 54	16	75	Clear	200	25	8
4KN42	56	43 x 48	16	75	Clear	200	25	8
5XL51	56	43 x 48	22	85	Black	150	15	10
4KN36	60	38 x 60	14	55	Clear	200	25	8
4KN37	60	38 x 60	16	75	Clear	200	25	8
5XL49	60	38 x 60	22	85	Black	150	15	10
4CU29	60	38 x 60	22	85	Clear	150	15	10

Call or visit your local branch or go to granger.com/toughguy for complete product line information.

©2019 W.W. Grainger, Inc. W-BUPX115-01



GRAINGER.COM® | 1.800.GRAINGER

