



## Insulated Universal Combination Pliers, 8-Inch



Be protected from up to 1,000 volts of electric current when working near energized sources with Klein's 8-Inch Insulated Universal Combination Pliers. These pliers offer flame-retardant handles, a toothed pipe grip and a high-leverage design, with the rivet closer to the cutting edge for 40% greater cutting and gripping power than other pliers designs. The durable, molded insulation meets or exceeds IEC 60900 and ASTM F1505 standards for insulated tools.

### Specifications

<b>Type:</b>	High-Leverage Pliers	<b>Application:</b>	ACSR, Screws, Nails and Most Hardened Wires
<b>Special Features:</b>	Integral Guards Help Prevent Hand Contact With Conductive Parts	<b>Overall Length:</b>	8.76" (22.3 cm)
<b>Material:</b>	Induction Hardened Steel	<b>Nose Type:</b>	Universal
<b>Jaw Length:</b>	1.78" (4.5 cm)	<b>Jaw Width:</b>	1.02" (2.6 cm)
<b>Jaw Thickness:</b>	0.55" (1.4 cm)	<b>Knife Length:</b>	0.711" (1.8 cm)
<b>Cut Style:</b>	Side-Cutting	<b>Joint Type:</b>	Hot-Riveted
<b>Handle Color:</b>	Orange	<b>Handle Finish:</b>	2-Layer Insulation
<b>Insulated:</b>	Yes	<b>Standards:</b>	IEC 60900 and ASTM F1505
<b>Weight:</b>	1.0 lb (0.5 kg)		