



Basic 1000V Insulated Tool Kit, 1000-Volt, 8-Piece



The kit of insulated tools incorporates all the Klein quality design and construction features that professionals have relied on. The tools combine excellent functionality along with reduction of risk of injury where a tool might make contact with an energized source with voltage up to 1000 volts. The high-dielectric white inner layer is a thick, exceptionally tough base coating which is bonded to the tool. The outer layer is a flame-resistant, bright orange color. All Klein insulated tools comply with the IEC 60900 and ASTM F 1505 standards for insulated tools. The 11045INS Insulated Wire / Stripper Cutter will strip and cut 10-18 AWG solid wire. The Wire Stripper also has holes for easily looping and bending wire. The D203-8INS 8in. Insulated Long-Nose Side Cutting Pliers have a unique slim head for working in confined areas.

Specifications

Application:	General Application Near Energized Source	Special Features:	Includes Durable Nylon Case
Included:	<ul style="list-style-type: none"> • 33536 Tool Case • D213-9N-EINS Linemans Plier • D228-8-INS High Leverage Diagonal Cutting Plier • D203-8N-INS Needle Nose Plier • 601-4-INS Slotted Screwdriver • 602-4-INS Slotted Screwdriver • 603-4-INS Phillips Screwdriver • 63050-INS High Leverage Cable Cutter • 11045-INS Wire Stripper 	Insulated:	Yes
Overall Width:	15.5" (39.4 cm)	Standard:	IEC 60900: 2012, ASTM F1505-10
Weight:	6.9 lb (3.1 kg)		
Handle Material:	High-Dielectric Plastic	Handle Color:	Orange
Overall Length:	11" (27.9 cm)	Overall Height:	2.5" (6.4 cm)