## **IEC Pin and Sleeve**

# 20A, 3 Phase Y, 277/480V, 4 Pole, 5 Wire

# Watertight Connector Body

## Features

- UL Type 4X, 12 and IP69k environmental ratings
- · Impact and corrosion resistant insulated non-metallic housing
- Watertight neoprene glad seal to prevent water ingress from entering at cable entrance
- Sequential contact engagement to prevent a momentary over-voltage
- Market leading UL witnessed HP ratings

## **Ordering Information**

DescriptionUPCWatertight IEC Pin and Sleeve783585405308Connector Body783585405308

Catalog Number HBL520C7W

## Listings

UL Listed, File E146033 CSA Certified File LR280C UL Classified to IEC 60309-1 IEC 60309-2

## **Specifications**

Housing Cord Clamps Glands Covers Gaskets PBT PBT Solid Neoprene PBT Santoprene

#### Performance

#### Electrical

Current Interrupting

Dielectric Voltage Max. Working Voltage

#### Mechanical

Impact Resistance Product Identification

Terminal Identification

## Environmental

Flammability Ingress Protection Moisture Resistance Operating Temperatures Certified for current interrupting at full rated current Withstand 3000V AC 600V RMS

Per CSA C22.2 No. 182.1 / UL1682 Identification and ratings are a permanent part of the device housing Terminals identified in accordance with North American and IEC conventions

# V-0

TYPE 3R,3RX,4X AND IP68,IP69K IEC 60309-1 Maximum Continuous 75°C; Minimum - 40°C w/o impact





**Wiring Device-Kellems** 

# HUBBELL