

# INSULATED 14 PIECE SET IN ZIPPER CARRY CASE



Tools that work for you

Insulated 14 Piece Tool Set Includes Slotted & Phillips Screwdrivers, Inch Nut Drivers, Pliers & Cutters in zipper carry case

**SKU: 32192      Grainger #: 1YUL6**

**Insulation Standards:** EN/IEC 60900, ASTM F-1505-10, VDE 0682/part 201, NFPA70E & CSA



## Details

- Insulation 10,000 Volt Tested & 1000 Volt Rated
- Insulated Tools Individually Tested For Insulation Integrity
- Vinyl Zipper Carry Case
- Professional Quality Tools - Made By Wiha

## Screwdrivers

- Ergonomic Wiha SoftFinish multi-component handle with roll-off protection
- Cushioned Grip For maximum comfort and power, perfect fit for your Hand because of Wiha handle size concept
- Wiha special chrome-vanadium-molybdenum tool steel



## Pliers & Cutters

- High quality forges C70 tool steel
- Induction hardened cutting edges and jaws
- Two component soft comfort grips with molded on slip guard for added user protection

Weight (lbs)	5.50000
RoHS Compliant	Yes
Head Type	slotted, phillips & nut drivers
Pieces In Set	14
UPC	084705321929
UNSPSC	27112135

## Pliers & Cutters

- 6.3" Long Nose Pliers With Cutters
- 8.0" Long Nose Pliers With Cutters
- 6.3" Diagonal Cutters
- 8.0" Combination Pliers

## Slotted Screwdrivers

- Insulated Slotted 3.0mm
- Insulated Slotted 4.5mm
- Insulated Slotted 6.5mm

## Inch Nut Drivers

- Insulated Nut Drivers 1/4"
- Insulated Nut Drivers 5/16"
- Insulated Nut Drivers 11/32"
- Insulated Nut Drivers 3/8"
- Insulated Nut Drivers 1/2"

## Phillips Screwdrivers

- Insulated Phillips #1
- Insulated Phillips #2



Vinyl Zipper Carry Case

## Insulated Pliers & Cutters



Safety slip guard



Soft grip ergo designed handle body

C70 Tool Steel

Cutters additionally induction hardened



Hard chrome finish for long lasting corrosion protection

## Slotted & Phillips Screwdrivers

### Insulation Test Standards:

Insulation according to EN/IEC 60900, ASTM F-1505, New VDE 0682/part 201, DIN 7437, NFPA70E & CSA

Insulation Molded directly onto the blade for permanent bonding



### Blade

CVM tool steel, hardened to average 58/60RC

● **Slotted:** 3.5, 4.5, 6.5mm

⊕ **Phillips:** #1, #2

○ **Inch Nut Drivers:**  
1/4, 5/16, 11/32,  
3/8, 1/2"