



Cut



Medium Duty

Enhanced safety due to the high visibility, cut performance and Level 1 thermal protection.

- HyFlex® 11-200 offers the most comfortable sleeve in the Ansell range. Generous space in the arm area reduces sweat and itchiness
- The anatomic design with adjustable forearm area enables freedom of movement so workers can do the job without constraints, increasing productivity
- Enhanced safety is assured, thanks to a high visibility sleeve with Level EN Cut 5 performance (ANSI A3) and Level 1 thermal protection (EN407)
- Better abrasion resistance (Level 2) and washability mean HyFlex® 11-200 offers improved total cost of ownership
- Due to its ergonomic design and fixing system, worker acceptance will increase, leading to fewer accidents and injuries



Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication

Applications

- Handling structural and body components
- Inspection, selecting, checking parts
- Body panel repair and replacement
- Glass repair and replacement
- Seizing structural and body parts
- Inspection (picking, checking and marking)
- Touching up
- Press shop operations
- Metalwork, glass processing

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-200

Ansell's most comfortable cut-resistant and high-visibility sleeve.

Key Features

- **Comfort:** The most comfortable sleeve in Ansell range - through generous space in the arm area reducing sweat and itchiness
- **Freedom of movement:** Anatomic design enables freedom of movement so that workers can do the job without constraints
- **Safety and longevity:** High visibility in a cut resistant sleeve with a prolonged wear life due to the Level 2 in abrasion resistance

Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
HyFlex® 11-200	Liner Material: Nylon, Polyester, Fiber glass Cuff Style: Knitwrist without thumbslot	13	19in	190" - 475 mm	• 12 pieces in a bag; 6 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

