

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-840

Our best seller in general handling



Multi Purpose Abrasion Protection Ergonomic Protection



Light Duty

These industrial hand gloves provide extreme durability for extended wear in abrasive applications, now with up to 20% higher abrasion protection

- These industrial hand gloves offer Fortix™ Abrasion Resistance Technology for enhanced durability
- Ideal nitrile-coated work gloves with up to 2x the grip for safer handling
- Enhanced breathability for even better comfort



Industries

- Aerospace
- Automotive
- Machinery and Equipment
- Metal fabrication
- Automotive Aftermarket
- Emergency Medical Services
- Food Processing
- Oil and gas
- Utilities
- Warehousing

Applications

- Assembly of small parts
- General handling
- Raw material handling
- Picking, fastening components
- Adjusting systems and screwing

Key Features

- Improved abrasion protection: provides 20% more abrasion for longer lasting handling in abrasive conditions
- Enhanced grip: up to 2 times more grip in dry environments for secure handling and a safer day at work
- Thin FORTIX™ nitrile foam coating: the new and improved coating is softer which increases flexibility and comfort. The 1.25 mm nitrile coating provides up to 2 times more grip and offers 20% longer wear time.
- Ergonomic fit: Optimized knitting at the base of the pinky finger across the finger tips and through the palm matches natural hand contours
- Ultimate comfort: Ansell ZONZ™ Comfort Fit Technology optimizes the knitting in selecting zones of the liner improving support, breathability and range of movement
- Silicone free: no transfer of silicone contaminants to metal parts prior to painting
- Clean and Skin Friendly: benefits from proprietary washing process that efficiently extracts impurities to deliver a cleaner, more comfortable glove.
- Oeko-Tex and Dermatest certified
- DMF Free

Technologies

 **ANSELL GRIP™**
Ansell Grip Technology

 **ERGOFORM™**
Ergonomic Design Technology

 **FORTIX™**
Abrasion Resistance Technology

 **ZONZ™**
Comfort Fit Technology

Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-840	Finishing: Palm Coated Coating Material: Foam Nitrile Liner Material: Nylon, Spandex Cuff Style: Knitwrist	15	5, 6, 7, 8, 9, 10, 11, 12	200-275 mm/ 8-11 inches	Black	<ul style="list-style-type: none"> 12 pairs in a bag; 12 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Gro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699