



**MCR
SAFETY**

N9695

Ninja

**Supported / Dipped gloves
Specification Sheet**

PRODUCT DESCRIPTION:

MCR Safety Ninja® gloves are engineered to provide the highest level of innovation. Each of the offerings in the Ninja® series include a unique shell and polymer combination incorporating the latest in hand protection technology. Our Ninja® Glove Line offers the greatest assortment of dexterity, sense of touch, and protection. The Ninja® Coral features a 15 gauge Hi-Vis Orange nylon shell, 7 gauge acrylic Terry interior, black coral 3/4 coating over premium clear PVC full dip.

FEATURES:

- Hi Visibility Orange Nylon Shell
- Insulated 7 Gauge Acrylic Terry Interior
- Black Coral 3/4 Dipped Coating with Clear PVC Full Dip
- Oil Resistant

APPLICATIONS:

Frozen food packaging, Agriculture, Bottling, Cold storage applications, Construction, Material Handling, Canning, Oil and Gas Industry



TECHNICAL DATA FOR: N9695

Series	Ninja
Material Group	Supported
Product Type	Supported / Dipped gloves
Glove Size	Large
Gauge	15 / 7 Gauge
Material	Nitrile
Insulated	Insulated
Lining	Acrylic

EN 388 : CE Score - Abrasion	3
EN 388 : CE Score - Cut	2
EN 388 : CE Score - Tear	3
EN 388 : CE Score - Puncture	1
ANSI Cut	ANSI Cut A3
ANSI Puncture	ANSI Puncture 2
ANSI Abrasion	ANSI Abrasion 4

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

N9695

Ninja

Supported / Dipped gloves
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
N9695L	Large	10.228	5.629	N/A	39.000 lb.	6.500
N9695M	Medium	9.843	5.355	N/A	35.988 lb.	5.998
N9695XL	X - Large	11.024	5.827	N/A	41.022 lb.	6.837
N9695XXL	XX - Large	11.417	6.141	N/A	43.520 lb.	7.253

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved