



**MCR  
SAFETY**

**3601K**

**Drivers  
Specification Sheet**

**PRODUCT DESCRIPTION:**

This supple leather contains natural lanolin that helps create a very soft feel. Characteristics include strongest tensile strength and excellent tactile sensitivity. Best combination of flexibility and comfort. The 3601K series features premium grade grain goatskin leather, 13 gauge DuPont™ Kevlar® Liner, shirred elastic back, and straight thumb.

**FEATURES:**

- Premium Grade Grain Goatskin
- 13 gauge DuPont™ Kevlar® Liner
- Straight Thumb
- Shirred Elastic Back, Color-coded hem to identify size

**APPLICATIONS:**

Aerospace, Carpentry, Cold storage applications, Farming, Landscaping, Construction, Manufacturing



**TECHNICAL DATA FOR: 3601K**

<b>Material Group</b>	Leather
<b>Product Type</b>	Drivers
<b>Glove Size</b>	Large
<b>Gauge</b>	13 Gauge
<b>Material</b>	Leather
<b>Leather Cut</b>	Grain
<b>Leather Type</b>	Goat Skin
<b>Grade</b>	Premium
<b>Features</b>	Sewn With KEVLAR
<b>Insulated</b>	Insulated
<b>Lining</b>	Kevlar
<b>Pattern</b>	Gunn
<b>Thumb Style</b>	Straight

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2018 MCR Safety - All Rights Reserved



**MCR**  
**SAFETY**

# 3601K

**Drivers**  
**Specification Sheet**



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
3601KL	Large	9.750	6.255	N/A	33.690 lb.	3.369
3601KM	Medium	9.250	5.700	N/A	28.220 lb.	2.822
3601KS	Small	8.81	5.380	N/A	26.540 lb.	2.654
3601KXL	X - Large	9.850	6.255	N/A	35.950 lb.	3.595
3601KXXL	XX - Large	10.000	6.625	N/A	37.170 lb.	3.717
3601KXXXL	XXX - Large	10.375	6.563	N/A	39.420 lb.	3.942

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2018 MCR Safety - All Rights Reserved