

**STANDARD FLEXIBLE DUCTING 20" X 25'**  
AM-DS2025**Product Description**

Industry standard quality ducting for everyday use. Single ply, PVC vinyl-coated polyester fabric with 15-gage spring steel wire helix and external PVC wearstrip. PVC coated polyester fastening cuffs at both ends with industry standard spring buckle cinches. Flame retardant. Available in 8" (15', 25'), 12" (15', 25') and 20" (25') sizes. Integrated carrying bags available with 8"X 25', 12"X 25' and 20"X 25' ducts.

**Features****Specifications**

<b>Brand</b>	Schaefer
<b>Rpm 60 Hz Motor</b>	20' = 430, 40'GP = 890, 40'HC = 1035
<b>Maximum Fan Diameter (inches)</b>	20
<b>Maximum Duct Length (feet)</b>	25

<b>Diameter (inches)</b>	20
<b>Product Dimensions (I X W X H Inches)</b>	20" x 25"
<b>Product Net Weight (lbs)</b>	TBD
<b>Product Color</b>	Yellow

<b>Duct Wire Pitch (inches)</b>	6
<b>Country Of Origin</b>	China