

UTILITY GRADE, HIGH ADHESION MASKING TAPE

TYPICAL APPLICATIONS

- For general purpose packaging, bundling, holding, splicing, tabbing and banding applications involving a variety of substrates
- Not recommended for exacting industrial masking, spray painting or oven-baking applications

PRODUCT FEATURES

- High adhesion
- Excellent quick stick
- Easy to use on multiple surfaces
- Water- and oil-resistant

CONSTRUCTION

Overall Grade/Function: Utility
Backing: Crepe paper
Adhesive: Synthetic rubber-based

STANDARD WIDTH(S)

6 mm 12 mm 18 mm 24 mm 36 mm 48 mm

STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

APPLICABLE STANDARDS

ASTM D 6123/D 6123M-97 (2012), Type I

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



PHYSICAL PROPERTIES	STANDARD	METRIC
Tensile Strength	20 lbs/in width	35.0 N/10 mm
Adhesion to Stainless Steel	49 oz/in width	5.36 N/10 mm
Thickness	5.0 mils	0.13 mm
Elongation	8%	8%
Service Temperature Range	50 F to 150 F	10 C to 66 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

