

NSYTRAL42

PLUG-IN BRIDGE, 2 POINTS FOR 4 MM² TERMINAL BLOCKS, RED



Main

Range	Lineryg
Product name	Lineryg TR
Product or Component Type	Plug-in bridge
Device short name	TRA
Accessory / separate part category	Connection accessory
Product compatibility	TRV screw terminal terminal block TRP push-in terminal block TRR spring terminal terminal block TRH IDC terminal block
Number of ways	2 ways

Complementary

Cable cross section	0.01 in ² (4 mm ²)
Number of connections	4 3 2
Number of measurement input	3 2 6 1 4
Quantity per Set	Set of 10
Net Weight	0.07 oz (2 g)
Color	Red

Ordering and shipping details

Category	21715 - IEC TERMINAL BLOCKS-NSY,AM1,DF6,GK1
Discount Schedule	CP5
GTIN	3606480534133
Nbr. of units in pkg.	1
Package weight(Lbs)	0.07 oz (2 g)
Returnability	Yes
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.97 in (5 cm)
Package 1 width	5.91 in (15 cm)
Package 1 Length	6.69 in (17 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Weight	0.22 lb(US) (0.1 kg)
Package 2 Height	1.97 in (5 cm)
Package 2 width	5.91 in (15 cm)
Package 2 Length	6.69 in (17 cm)
Unit Type of Package 3	S01
Number of Units in Package 3	2000

Package 3 Weight	8.94 lb(US) (4.053 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------