

EXTREME TEMPERATURE, MULTIPLE APPLICATION

PERFORMANCE CARTON SEALING TAPES

You insist on superior performance from your carton sealing tape. No matter the application or the temperature conditions in which you seal or send, you expect a reliable and secure seal. It's why AP Series acrylic carton sealing tapes from Shurtape® are crafted to perform – whether you need strength for bulky packages or a quick stick on corrugated boxes.

From light to heavy duty applications, AP Series is perfect for any job. It's engineered to bond well in temperatures ranging from -20 F to 180 F, and is available in six grades that range in thickness from 1.6 mils to 2.5 mils.

UV resistant to protect against yellowing, AP Series protects labels and printed surfaces from weather and handling, and is designed to give you the long-lasting performance you demand.









AP SERIES

SHURTAPE.COM 1.888.442.TAPE

Shurtape®
TRUE TO YOUR WORK™

EXTREME TEMPERATURE, MULTIPLE APPLICATION

PERFORMANCE CARTON SEALING TAPES

			Tensile	Adhesion to Stainless Steel	Thickness	Elongation
AP 15		<p>Protecting shipping labels and other printed surfaces from weather and handling</p> <ul style="list-style-type: none"> • High clarity, low odor, non-yellowing acrylic adhesive • UV-resistant • Excellent aging characteristics for long-term use • Application temperature range of 20 F to 110 F • Service temperature range of -20 F to 180 F 	20 lbs/in width	19 oz/in width	1.6 mils	150%
AP 101®		<p>Automated or manual sealing of non-critical, lightweight cartons</p> <ul style="list-style-type: none"> • High clarity, low odor, non-yellowing acrylic adhesive • UV-resistant • Excellent aging characteristics for long-term use • Application temperature range of 20 F to 110 F • Service temperature range of -20 F to 180 F 	20 lbs/in width	18 oz/in width	1.6 mils	150%
AP 180®		<p>Automated or manual sealing of lightweight cartons</p> <ul style="list-style-type: none"> • High clarity, low odor, non-yellowing acrylic adhesive • UV-resistant • Excellent aging characteristics for long-term use • Application temperature range of 20 F to 110 F • Service temperature range of -20 F to 180 F 	20 lbs/in width	21 oz/in width	1.8 mils	150%
AP 201®		<p>Automated or manual sealing of light- to medium-weight cartons</p> <ul style="list-style-type: none"> • High clarity, low odor, non-yellowing acrylic adhesive • UV-resistant • Excellent aging characteristics for long-term use • Application temperature range of 20 F to 110 F • Service temperature range of -20 F to 180 F 	24 lbs/in width	22 oz/in width	2 mils	150%
AP 301®		<p>Automated or manual sealing of medium-weight cartons in extreme temperatures or exposed to handling stress</p> <ul style="list-style-type: none"> • High clarity, low odor, non-yellowing acrylic adhesive • UV-resistant • Excellent aging characteristics for long-term use • Application temperature range of 20 F to 110 F • Service temperature range of -20 F to 180 F 	27 lbs/in width	25 oz/in width	2.2 mils	150%
AP 401®		<p>Heavy duty automated or manual sealing of cartons exposed to rough handling and load stress</p> <ul style="list-style-type: none"> • High clarity, low odor, non-yellowing acrylic adhesive • UV-resistant • Excellent aging characteristics for long-term use • Application temperature range of 20 F to 110 F • Service temperature range of -20 F to 180 F 	30 lbs/in width	27 oz/in width	2.5 mils	150%



SHURTAPE.COM 1.888.442.TAPE    

Shurtape®
TRUE TO YOUR WORK™