



Item # IM-20

Non-Sparking, Non-Magnetic, Corrosion Resistant
1000V Rated (Adjustable Wrenches are not 1000V Rated)

Set Includes:

- **Adjustable Combination Wrench, 8"**: IP-31
- **Linemans'/Side Cutting Pliers, 8-1/2"**: IP-35
- **Diagonal Cutting Pliers, 7"**: IP-36
- **Groove Joint Pliers, 10"**: IP-39
- **#2 Phillips Screwdriver: IS-1099**
- **Standard Screwdriver, 5/16" Tip: IS-49**
- **Standard Socket, 6-Point, 3/8" Drive, 7/16"**: ISS-3/8D7/16
- **Standard Socket, 6-Point, 3/8" Drive, 1/2"**: ISS-3/8D1/2
- **Standard Socket, 6-Point, 3/8" Drive, 9/16"**: ISS-3/8D9/16
- **Ratchet Wrench, 3/8" Drive: IW-142R**
- **Extension Bar, 3/8" Drive: IWE-3/8X6**
- **Adjustable Wrench, 8"**: IW-71
- **Adjustable Wrench, 10"**: IW-72
- **Single Box End Wrench, 12-Point, 7/16"**: IWSB-7/16
- **Single Box End Wrench, 12-Point, 1/2"**: IWSE-1/2
- **Single Box End Wrench, 12-Point, 9/16"**: IWSE-9/16
- **Toothbrush Style Scratch Brush with Wooden Handle: TB-10**
- **Tool Box: M-49-BOX**



Specifications

-

length (mm)	405
width (mm)	235
height (mm)	205
Wt (g)	4990
length (in)	16
width (in)	9-1/4
height (in)	8
Wt (lbs)	11.00