



**MCR
SAFETY**

3204K Memphis Drivers Specification Sheet

PRODUCT DESCRIPTION:

From wranglin' to buildin', these gloves are tough for the job! Cowhide is the most commonly used leather due to availability. Characteristics include a good balance between abrasion resistance, dexterity, durability and comfort. The 3204K drivers gloves feature; premium cow grain leather, sewn with Dupont™ Kevlar®, lined with a 7 gauge Kevlar® fiber liner, shirred elastic back, cotton hemmed, and a keystone thumb pattern.

FEATURES:

- Premium Grade Grain Cowhide
- Sewn with Kevlar® thread
- 7 Gauge Kevlar® Fiber Lining
- Keystone Thumb
- Color-coded hem to identify size

APPLICATIONS:

Aerospace, Carpentry, Cold storage applications, Farming, Landscaping, Construction, Manufacturing



TECHNICAL DATA FOR: 3204K

Series	Memphis
Material Group	Leather
Product Type	Drivers
Glove Size	Large
Material	Leather
Leather Cut	Split Leather
Leather Type	Cow Skin
Grade	Select Grade
Features	Sewn With KEVLAR
Insulated	Insulated
Lining	Kevlar
Pattern	Gunn
Thumb Style	Keystone

ANSI Cut	ANSI Cut A2
ANSI Puncture	ANSI Puncture 3
ANSI Abrasion	ANSI Abrasion 6
ANSI Contact Heat	Level 3 (Applications less than 392 degrees F)

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

3204K

Memphis

Drivers

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
3204KL	Large	10.11	6.94	N/A	53.200 lb.	5.320
3204KM	Medium	9.33	5.92	N/A	56.000 lb.	5.600
3204KS	Small	8.81	5.81	N/A	44.940 lb.	4.494
3204KXL	X - Large	9.60	6.50	N/A	55.920 lb.	5.592
3204KXXL	XX - Large	10.480	7.010	N/A	61.440 lb.	6.144

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved