

INSULATED 80 PIECE SET IN ROLLING TOOL CASE



Tools that work for you

Insulated 80 Piece Tool Set Includes Screwdrivers, Pliers & Cutters, Ruler, Knife & Sockets in 22" L x 13-3/4" W x 9" H Rolling Tool Case

SKU: 32800 **Grainger #: 26X224**

Details

- Insulation 10,000 Volt Tested & 1000 Volt Rated
- Insulated Tools Individually Tested For Insulation Integrity
- Lockable Rolling Water Tight Case Keeps Your Tools Secure
- Custom Molded Rolling Carry Case - Job Site Solution
- Each Tool Has Dedicated Position For Easy Storage & Retrievals
- Professional Quality Tools - Made By Wiha

Insulation Standards: EN/IEC 60900, ASTM F-1505-10, VDE 0682/part 201, NFPA70E and CSA



Pliers & Cutters

- 6.3" Long Nose Pliers
- 8.0" Long Nose Pliers
- 6.3" Long Flat Nose Pliers
- 6.3" Bent Nose Pliers
- 6.3" Stripping Pliers
- 8.0" Adjustable Wrench
- 9.0" Combo Pliers/Crimpers
- 6.3" Diagonal Cutters - Dynamic Joint
- 8.0" High Leverage Cutters - Dynamic Joint
- 6.3" Cable Cutters - Dynamic Joint

Slotted Screwdrivers

- Insulated Slotted 2.5mm
- Insulated Slotted 3.0mm
- Insulated Slotted 3.5mm
- Insulated Slotted 4.0mm
- Insulated Slotted 4.5mm
- Insulated Slotted 5.5mm
- Insulated Slotted 6.0mm
- Insulated Slotted 6.5mm
- Insulated Slotted 8.0mm
- Insulated Slotted 10.0mm

Phillips Screwdrivers

- Insulated Phillips #0
- Insulated Phillips #1
- Insulated Phillips #2
- Insulated Phillips #3

Terminal Block Screwdrivers

- Insulated Sit/Ph Terminal #1
- Insulated Sit/Ph Terminal #2

Inch Nut Drivers

- Insulated Nut Driver 7/32"
- Insulated Nut Driver 1/4"
- Insulated Nut Driver 5/16"
- Insulated Nut Driver 3/8"
- Insulated Nut Driver 7/16"

Metric Nut Drivers

- Insulated Nut Driver 5.0mm
- Insulated Nut Driver 5.5mm
- Insulated Nut Driver 6.0mm
- Insulated Nut Driver 7.0mm
- Insulated Nut Driver 8.0mm
- Insulated Nut Driver 10.0mm
- Insulated Nut Driver 13.0mm

Hex Inch T-Handles

- Insulated T-handle Hex 5/32"
- Insulated T-handle Hex 3/16"
- Insulated T-handle Hex 7/32"
- Insulated T-handle Hex 1/4"
- Insulated T-handle Hex 5/16"
- Insulated T-handle Hex 3/8"

Hex Metric T-Handles

- Insulated T-handle Hex 4.0mm
- Insulated T-handle Hex 5.0mm
- Insulated T-handle Hex 6.0mm
- Insulated T-handle Hex 8.0mm

Torx Screwdrivers

- Insulated Torx T6
- Insulated Torx T7
- Insulated Torx T8
- Insulated Torx T9
- Insulated Torx T10
- Insulated Torx T15
- Insulated Torx T20
- Insulated Torx T25
- Insulated Torx T30

Square Screwdrivers

- Insulated Square #1
- Insulated Square #2

Weight (lbs)	33.9000
RoHS Compliant	Yes
Head Type	slotted, phillips, hex metric, hex inch, torx, square, terminal block, nut driver inch, nut driver metric
Pieces In Set	80
UPC	084705328003
UNSPSC	27112135

Inch Sockets

- Insulated Socket 1/2"
- Insulated Socket 9/16"
- Insulated Socket 5/8"
- Insulated Socket 11/16"
- Insulated Socket 3/4"
- Insulated Socket 13/16"
- Insulated Socket 7/8"

Metric Sockets

- Insulated Socket 13mm
- Insulated Socket 14mm
- Insulated Socket 15mm
- Insulated Socket 17mm
- Insulated Socket 19mm
- Insulated Socket 20mm
- Insulated Socket 22mm

Accessories

- Insulated Ratchet 3/8" Drive
- Insulated 4.9" Extension 3/8" Dr.
- Insulated L-key 10mm
- Insulated L-key 1/2"
- Single Pole Voltage Detector-110V to 250V
- Insulated Cable Knife 50mm
- 2 Meter Ruler In/MM

