


CAT. #	COLOR	Ø D
5385-0	GRAY AKZO NOBEL# JW107N	.62 [15.7]
5386-0	GRAY AKZO NOBEL# JW107N	.84 [21.3]
5387-0	GRAY AKZO NOBEL# JW107N	1.03 [26.2]

#8 - 32 UNC-2A X 1/4" CROSS RECESSED UNDERCUT FLAT COUNTERSUNK HEAD, SELF TAPPING SCREW-TYPE F (QTY. 2)





#10-32UNF-2A X 3/8" HEX WASHER SELF TAPPING TRILOBULAR GROUNDING SCREW

CLOSURE PLUG (QTY. 2)

BOX MOUNTING LUG (QTY. 2)



OUTLET SIZE (SEE TABLE BELOW)



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
SINGLE GANG DEEP BOX	DIE-CAST ALUMINUM	PAINT
GROUNDING SCREW	C1022 STEEL	GREEN ZINC AERODITE
CLOSURE PLUG	LEXAN/ZINC	SEE TABLE
MOUNTING LUG	CRCA	N/A
MOUNTING LUG SCREW	C1022 STEEL	.00015" ZINC PASSIVATION

GRAY BOX	CLOSURE PLUG 1/2" & 3/4" NPT	
	MATERIAL	FINISH
PRIMARY	LEXAN	GRAY
ALTERNATE	ZINC	NATURAL

GRAY BOX	CLOSURE PLUG 1" NPT	
	MATERIAL	FINISH
PRIMARY	ZINC	NATURAL

- NOTES:
- ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 - BOX VOLUME: 22.50 IN³ [368.7 CM³]
 - UL & CSA LISTED.

OUTLETS			
CAT. #	OUTLET SIZE	OUTLET LOCATION	OUTLET QTY.
5385-0	1/2" - 14 NPT	A,B & C	1
5386-0	3/4" - 14 NPT	A,B & C	1
5387-0	1" - 11.5 NPT	A,B & C	1

SYMBOL	INITIAL RELEASE	S.J.	07/12/17
	REVISION DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
SINGLE GANG DEEP WITH 3-HOLE RECT. BOX

TOLERANCE UNLESS OTHERWISE SPECIFIED
.XX DECIMAL ±.015
.XXX DECIMAL ±.005
ANGLE ±2°

RACO
South Bend, Indiana

DRAWN BY:	F.P.	SCALE:
APP. BY:	S.J.	1:2
DATE:	07/12/2017	

FILE NO. :
SINGLE GANG DEEP BOX WITH 3 OUTLETS CUS

DIMENSION SHEET FOR CAT. NO.
SEE CHART

SIZE:
B