

Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding Valise Connector Body

HUBBELL

Features

- Hinged one piece body design for easy assembly
- Powerful, offsetting cord grips clamp on individual conductors
- Assembly screws are captive and will not fall out while wiring

Ordering Information

| Description | Cord Diameter | UPC | Catalog Number |
|-------------|-----------------------|--------------|----------------|
| Black nylon | .220"-.660"(5.6-16.8) | 783585019307 | HBL5369VBK |



Listings

UL Listed to UL498 File E1706
CSA Certified to C22.2 No. 42 File 280C
NEMA® WD-6 Compliant

Resources

[eCatalog](#)

Specifications

| | |
|-----------------|------------------------------|
| Housing | Nylon |
| Contacts | Brass |
| Assembly Screws | Plated Steel |
| Cable Inserts | PPO |
| Terminal Screws | #8-32 Brass , multiple drive |
| Terminal Clamp | Nickel plated steel |
| Assembly Screws | Plated steel |

Performance

Electrical

| | |
|----------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage | Withstands 2,000V minimum |

Mechanical

| | |
|-------------------------|--|
| Product Identification | Ratings are a permanent part of the device |
| Terminal Accommodation | #18-#12 AWG stranded copper wire only |
| Terminal Identification | Terminals identified in accordance with UL 498 and CSA |

Environmental

| | |
|------------------------|---|
| Flammability | UL 94 HB or better |
| IP Suitability | IP20 |
| Operating Temperatures | Maximum continuous 75°C; minimum -40°C (w/o impact) |

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

