

SHOWA

S8115-16T

Light and breathable, yet highly cut resistant, the SHOWA S8115-16T is 16" long and features an elastic thumb loop and is perfect for operations requiring extended arm cut-resistance.

FEATURES

- 15-gauge seamless knit
- Engineered fiber with HPPE
- 16" sleeve
- Elastic thumb loop

BENEFITS

- Level A4 ANSI cut-resistance
- Excellent comfort and flexibility
- High Performance, cut-resistant fiber technology

INDUSTRY



Automotive



Food



Glass



Manufacturing



Mechanical

IDEAL APPLICATIONS

- Metal Stamping
- Food packing and handling
- Poultry, meat & seafood processing
- Handling glass and windows
- Plate glass production
- Bottling
- Canning
- HVAC



TAA PRODUCTS

MADE IN USA

MATERIAL

- Glass Fiber
- HPPE
- Seamless knit

COATING

- Uncoated

GRIP

- N/A

STANDARDS

ANSI / ISEA
105-2016



CUT

ANSI / ISEA
105-2016



PUNCTURE

SHOWA

S8115-16T



PACKAGING

- 2 Sleeves Per Polybag



SIZES

- M
- L
- XL



COLOUR

- Gray



[USER INSTRUCTIONS

Do not use where there are chemical, electrical, thermal or entanglement risks. Wash at 40°C max. Performance levels as per standard EN388 retained after 3 washes, subject to variations linked to actual usage conditions. The performance levels apply to the coated surface only. Store in a dry place, away from the light.

[DISCLAIMER

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

Get in touch

SHOWA USA | 579 Edison Street - Menlo, GA 30731, USA

USA@SHOWAgroup.com

© SHOWA Group 2018 | All rights reserved