

OPEN GEAR & WIRE ROPE LUBRICANT



LU™ 201



For use in extreme pressure applications



NSF® Registered; H2 Rated (Lubricants with no contact) (Registration # 131586)



Temperature Rating:
Low 0 °F (-18 °C) • High 450 °F (232 °C)



HMIS Hazard Rating:
Health (2) • Flammability (4) • Reactivity (0)

- Prevents rust & corrosion
- Withstands extreme pressure
- Will not become brittle or breakdown while working



PRESERVE. PROTECT. PREVENT.™

Sprayon® LU™ 201 Open Gear & Wire Rope Lubricant is a high performance lube that penetrates the pores of metal surfaces to reach the core of wire rope. This heavy duty lubricant provides a wide range of lubrication at high temperatures while adhering extremely well to surfaces. It “travels” on metal surfaces to actually displace water, resulting in excellent rust protection. Equipped with an extension tube for hard-to-reach areas or for use while equipment is in operation.

USES

- Open or exposed gears
- Gear boxes
- Wire rope
- Winches
- Cable
- Metal forming presses
- Roller chains
- Machine tools
- Wire rope
(in use or in storage)



LU201

© 2010 Sprayon® Products Made in U.S.A.

LUBRICANTS

APPLICATION

Maximum performance is achieved when the metal surfaces to be protected are clean, dry and free of rust, oil and mill scale. Aerosol Application: Product should be sprayed in a well ventilated area. Sprays best at room temperature (70°F.) Shake well before using. Spray at a distance of 10" to 14" from surface.

PERFORMANCE

- PLASTIC SAFE:** No
TEMPERATURE RANGE:
LOW: 0°F
HIGH: 450°F
LOAD CAPACITY: Extreme pressure
- NSF Registration Number 131586; H2 Rated
 - Penetrant
 - Water-Displacer
 - Rust Inhibitor
 - Quiets, lubricates and protects
 - Will not wash or weather away
 - Displaces moisture
 - Black color assists in showing complete coverage
 - Ideal for indoor or outdoor use
 - Equipped with an extension tube for hard-to-reach areas

PACKAGING

Stock #: S00201
UPC Code: 0-75577-90201-9
Fill Wt.: 12 oz.
Per Case: 12
Carton Dimensions:
L 10-7/8" x W 8-3/16" x H 8"

SHIPPING

Refer to section 14 of the material safety data sheet for proper transport information and labeling.

PROPERTIES

- APPEARANCE:** Viscous black film
ODOR: Mild solvent
PROPELLANT: Hydrocarbon
WT./GAL.: 6.16
SPECIFIC GRAVITY: 0.74
PAINTABLE: No
H.A.P.S. (Hazardous Air Pollutants): No
SARA 313 Chemicals: No
% VOC AEROSOL: 60.00%
V.O.C. COMPLIANT CALIFORNIA: Yes
V.O.C. COMPLIANT OTC STATES: Yes
FLAMMABLE: Yes
FLASH POINT: <0°F
HAZARD RATING: 2,4,0
SHELF LIFE: 3 years from date of manufacture

RESOURCES

- MSDS/EDS/PRODUCT DATA SHEETS:**
sprayon.com
CUSTOMER SERVICE:
1-800-777-2966
TECHNICAL INFORMATION:
1-800-251-2486



Distributed by:

PRESERVE. PROTECT. PREVENT.



Sprayon® Products

101 Prospect Ave. NW
Cleveland, OH 44115
Sprayon.com
1-800-777-2966

310-PDS-LU201