



**MCR
SAFETY**

9666 Memphis Dipped Specification Sheet

PRODUCT DESCRIPTION:

Economy PU coated Nylon provides good tactile sensitivity, dexterity, and abrasion resistance. They feature a 13 gauge Nylon shell with polyurethane palm and finger coating. These gloves come with color coded hem sizing and are individually poly bagged by the pair. Made without Silicone.

FEATURES:

- 13 Gauge Gray Nylon Shell
- Gray PU Coated Palm and Fingertips
- Individually poly bagged by the pair
- Color coded hem to identify sizes

APPLICATIONS:

Agriculture, Assembly Line Production, Automotive , Carpentry, Construction, Janitorial , Manufacturing, Material Handling



TECHNICAL DATA FOR: 9666

Series	Memphis	EN 388 : CE Score - Abrasion	4
Material Group	Strings	EN 388 : CE Score - Cut	1
Product Type	Dipped	EN 388 : CE Score - Tear	3
Glove Size	Large	EN 388 : CE Score - Puncture	1
Gauge	13 Gauge		
Material	Nylon		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

9666
Memphis
Dipped
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9666L	Large	10.04	5.28	2.83	10.872 lb.	0.906
9666M	Medium	9.65	5.12	2.76	10.548 lb.	0.879
9666S	Small	9.29	4.48	2.68	10.056 lb.	0.838
9666XL	X - Large	10.43	5.44	2.95	12.084 lb.	1.007
9666XS	X - Small	8.89	4.48	2.56	9.300 lb.	0.775
9666XXL	XX - Large	10.82	5.44	3.07	12.204 lb.	1.017

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved