

## KLEENGUARD\* A20 Breathable Particle Protection Coveralls, Lab Coats

### Product Information

Zipper Front	White Code	Vending Machine Ready	Blue Denim Code	Size	Qty
	35671 <sup>¥</sup>	--	--	S	24
	49002	--	58532	M	24
	49003	37711	58533	L	24
	49004	37712	58534	XL	24
	49005	37713	58535	2XL	24
	49006	47714	58536	3XL	20
	49007	37715	58537	4XL	20
	35670 <sup>¥</sup>	--	--	5XL/6XL	20

Zipper Front, Elastic Wrists & Ankles	White Code	Vending Machine Ready	Blue Denim Code	Size	Qty
	35810 <sup>¥</sup>	--	--	S	24
	49102	--	58502	M	24
	49103	37716	58503	L	24
	49104	37717	58504	XL	24
	49105	37718	58505	2XL	24
	49106	37719	58506	3XL	20
	49107	37720	58507	4XL	20
	30920 <sup>¥</sup>	--	23998	5XL	20
	27179 <sup>*</sup>	--	--	6XL	21
	35669 <sup>¥</sup>	--	--	5XL/6XL	20

Zipper Front, Elastic Back, Wrist, Ankles & Hood	White Code	Vending Machine Ready	Blue Denim Code	Vending Machine Ready	Size	Qty
	49112	43170	58512	--	M	24
	49113	43171	58513	--	L	24
	49114	41169	58514	41185	XL	24
	49115	41170	58515	41186	2XL	24
	49116	41171	58516	41187	3XL	20
	49117	43173	58517	--	4XL	20
	30924 <sup>¥</sup>	43174 <sup>*</sup>	30953 <sup>*</sup>	--	5XL	20

Zipper Front, Elastic Back, Wrists, Ankles, Hood & Boots	White Code	Blue Denim Code	Size	Qty
	49122	58522	M	24
	49123	58523	L	24
	49124	58524	XL	24
	49125	58525	2XL	24
	49126	58526	3XL	20
	49127	58527	4XL	20
	27258 <sup>¥</sup>	30910 <sup>*</sup>	5XL	20

### Product Information

Lab Coat	Code	Size	Qty
	35618 <sup>*</sup>	S	30
	35619	M	30
	35620	L	30
	35621	XL	30
	35622	2XL	30
	35623	3XL	30
	35624	4XL	30
	35625	5XL	30
	37427 <sup>*</sup>	6XL	30

- 4 hook and loop closure
- Elastic Wrists
- Knee length
- White

Lab Coat	Code	Size	Qty
	42201 <sup>*</sup>	XS	25
	30913 <sup>*</sup>	S	25
	10019	M	25
	10029	L	25
	10039	XL	25
	40049	2XL	25
	30930 <sup>¥</sup>	3XL	25
	30914 <sup>¥</sup>	4XL	25

- 4 snap closure
- Open Wrists
- Knee length
- Left chest pocket
- Right hip pocket
- White

Frock	Code	Size	Qty
	30926 <sup>¥</sup>	S	30
	36262	M	30
	36263	L	30
	36264	XL	30
	36265	2XL	30
	30937 <sup>*</sup>	3XL	30
	30933 <sup>*</sup>	4XL	30
	34815 <sup>¥</sup>	5XL	30

- 5 snap closure
- Elastic Wrists
- Below knee length
- Mandarin collar
- White

Smock	Code	Size	Qty
	36150	Universal	60

- Sonic seams
- Tie closure
- Elastic Wrists
- Knee length
- Open neck
- White


Apron	Code	Size	Qty
	36550	28"x40"	100 (10 pks/10)
	36260	28"x40"	100 (10 pks/10)

- Bound Neck & Ties
- White
- One Size fits all
- Denim with Pockets

\*Made-to-Order Codes


## KLEENGUARD\* A20 Breathable Particle Protection Coveralls, Lab Coats & Accessories – Cont'd


### Product Information - Continued

Hood	Code	Size	Qty
 • Elastic face seal • White	36890	Universal	100


Sleeve Protector	Code	Size	Qty
 • Elastic top & Wrists • 21" length ergonomically designed for improved fit • White	36870	21"	200

Boot Cover	Code	Size	Qty
 • Elastic opening • 13" height • Seamless sole • White • One size fits all	36880	Universal	300

Pants	Code	Size	Qty
 • Elastic Waist • Open ankle • White	36222	M	50
	36223	L	50
	36224	XL	50
	36225	2XL	50

Shirt	Code	Size	Qty
 • 5 snap closure • Open Wrists • Hip length • Mandarin collar • White	36212	M	50
	36213	L	50
	36214	XL	50
	36215	2XL	50

Shoe Cover	Code	Size	Qty
 • Fully elasticized for formed fit • 6.5" height • White • One size fits all	36885	Universal	300

Shoe Cover	Code	Size	Qty
 • Double-bagged for cleanroom use • Light blue color • Fully elasticized • NPFA 99 Compliant Antistatic Material	66857	Universal	75 pr/bag (3 bags/cs)
	66875	XL/2XL	75 pr/bag (3 bags/cs) 225 pr/cs

### Fabric Properties

Physical Properties	Test Method	Target
Tensile Strength – MD	ASTM D5034	20.9 lbs
Tensile Strength – CD	ASTM D5034	18.5 lbs
Trapezoidal Tear - MD	INDA IST 100.2	7.3 lbs
Trapezoidal Tear – CD	INDA IST 100.2	5.5 lbs
Elongation – MD	ASTM D5034	50.1%
Elongation – CD	ASTM D5034	58.2%
Lint - # of particles <sup>†</sup>	IEST-RP-CC003.4 Helmke Drum	≥0.3 µm - 1332 ≥0.5 µm - 967
Flammability	CPSC 1610	Class 1
Mullen Burst	ISO 13938-1	47.4 psi
Static Decay (<0.5sec)	NFPA 99	Pass

<sup>†</sup>Benchmark testing, sample size = 1

Barrier Properties	Test Method	Target
Hydrohead	AATCC 127-2008	72.9 cm
Particle Hold Out (3.0 – 5.0 µm)	Independent Lab	96.3%

Comfort Properties	Test Method	Target
Air Permeability	ASTM D737	41.5 cfm
WTVR	ASTM E96	4616 g/m <sup>2</sup> /24hr

Additional Attributes
Lightweight and breathable
Product not made with silicone
Not made with BHT preservative
Not made with natural rubber latex
Non-latex polyisoprene elastic
REFLEX* Design – see catalog for sizing chart
Seamless front
0.5" Zipper flap
Serged Seams

### Workmanship Requirements

Apparel shall be made in accordance with reasonable industry practice with respect to holes, tears, wrinkles, cleanliness, and foreign materials or dirt.

For Additional information: Contact your Kimberly-Clark representative, our Customer Service Team (888)-346-GOKC (4652) or [KCPInfo@kcc.com](mailto:KCPInfo@kcc.com)