



TMI INTERNATIONAL, LLC

PHYSICAL PROPERTY DATA SHEET

Product: 14
Description: Weld Screen Amber Flexible PVC

Property	Typical Value	Test Method
Specific Gravity	1.23	ASTM D-792
Shore 'A' Duro Hardness (15 sec delay)	80	ASTM D-2240
Tensile Strength (psi)	2700	ASTM D-412
Tensile Elongation (%)	380	ASTM D-412
100% Modulus (psi)	1500	ASTM D-412
UV Resistance	YES	
Operating Temperature	0-150 °F	

Notes:

Compliant with American Welding Society (AWS) specifications - AWS F2.3M-2019

The information contained herein is believed to be reliable but no representations, guarantees or warranties of any kind are made as to its accuracy, suitability for particular applications, or the results to be obtained there from. The information is based on laboratory work with small-scale equipment and does not necessarily indicate end product performance. Full-scale testing and product performance are the responsibility of the user. TMI International, LLC shall not be liable; the customer assumes all risk and liability of any use or handling of any material.

SELLER MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Nothing contained herein is to be considered as permission, recommendation, nor as an inducement to practice any patented invention without permission of the patent owner.

REV DATE 9-6-2022

PENNSYLVANIA
1.800.888.9750
5350 Campbells Run Rd
Pittsburgh, PA 15205

OHIO
1.866.929.1449
3333 Win St
Cuyahoga Falls, OH 44223

GEORGIA
1.888.606.7325
4708 S Old Peachtree Rd Ste 700
Norcross, GA 30071

CALIFORNIA
1.800.854.7951
14500 Miller Ave
Fontana, CA 92336