

Cycle Pliers

DIN ISO 5743

84

- > for very narrow screw connections
- > special tool steel; forged, oil-hardened

84 11 200
Straight head

84 21 200
20° angled head



84 11 200



84 21 200
 $\angle 20^\circ$

Product Number	Packaging	\leftrightarrow Inch mm		Pliers	Head	Handles	Recess Ø Inch Ø mm	Head thickness Inch mm	 lbs
84 11 200		8 200		black atramentized	polished	plastic coated	15/64 / 25/64 6 / 10	9/64 3.5	0.39
84 21 200		8 200	$\angle 20^\circ$	black atramentized	polished	plastic coated	15/64 / 25/64 6 / 10	9/64 3.5	0.40

KNIPEX SmartGrip®

Water Pump Pliers with automatic adjustment
DIN ISO 8976

85

- > ideal for frequent changeovers to workpieces of different sizes
- > automatic adjustment for one-hand operation both for right-handed and left-handed use
- > good access to the workpiece due to the slim dimensions in the head and joint area and flush joint bolt
- > self-locking on pipes and nuts: no slipping off the workpiece and low handforce required
- > gripping surfaces with special hardened teeth, teeth hardness (approx. 61 HRC): low wear and reliable gripping
- > box-joint design: high stability because of double guide
- > pinch guard prevents operators' fingers being pinched
- > locking lever for space saving transport with reliable closed handles
- > chrome vanadium electric steel; forged, multi stage oil-hardened



85 01 250 US

Adjustment to the workpiece is automatic with the KNIPEX SmartGrip®! Just grip the pliers handles and squeeze – it's that easy!



Product Number	Packaging	\leftrightarrow Inch mm	Pliers	Head	Handles	 Ø Inch Ø mm	 Inch mm	 lbs
85 01 250 US		10 250	grey atramentized	polished	non-slip plastic coated	1 1/4 32	1 13/32 36	0.82