

CHROME SLT®

SlipFit® cuff assists a quick on and off between tasks

Goatskin leather palm provides a traditional style of comfort

Aramid liner for 360° cut protection (interior layer)

Grip in dry or light oil situations

Form-fitting, quality materials






Back-of-hand impact guards provide ANSI/ISEA 138 Level 2 protection on knuckles and fingers

High dexterity



4060 Chrome SLT®

PROTECTION ZONES:

 Impact Protection	 Aramid Liner	ANSI/ISEA CUT A5	GRAM SCORE 2509
		ANSI/ISEA PUNCTURE 4	ANSI/ISEA 138 
<small>• Lab tested in accordance with HRC ATPV: 23.6 Cal/cm² for a level 2 performance</small>		EN388: 2016 2X23EP	EN407: 2004 X2XXX1
		Contact Heat Large splashes of molten metal	Level 2 Level 1

FEATURES:

HexArmor® Chrome SLT® gloves are built for a wide array of applications. Each product in the series was crafted to fit the hand with a specific purpose. With multiple styles and various safety features, you can be confident that the Chrome SLT® will keep your hands protected against almost any hazard. Our Chrome SLT® gloves were designed with ultimate comfort in mind, providing unsurpassed dexterity while maintaining cut and puncture resistance. With options for cold weather protection, your hands can stay safe and comfortable in any environment.

ATTRIBUTES:

Style:	Mechanics
Grip:	Dry or light oil
Cuff Style:	SlipFit®
Sizes:	6/XS through 14/5XL

HexArmor®

Call 1-877-MY ARMOR or visit hexarmor.com

HexArmor® products are cut and puncture resistant, NOT CUT AND PUNCTURE PROOF. Do not use with moving or serrated blades or tools. User shall be exclusively responsible to assess the suitability of the product as specified for any individual application or use. Protection zones are to be used as a general guide. Actual product protection zones may differ. Product features, design, protection zones subject to change.

Protected by patents and patents pending