

SHOWA
910C

The SHOWA 910C combines top-of-the-line stainless steel, a specialized wrapping process and a PVC dotted coating to provide cutting-edge grip and ANSI Cut Level A6 protection.

FEATURES

- 10-gauge stainless steel cut-resistant knit with steel engineered fiber
- PVC dotted coating
- Ambidextrous
- Fully launderable

BENEFITS

- Level A6 ANSI cut-resistance
- Superior cut protection with a special wrapping process

INDUSTRY



Automotive



Mechanical



Metallurgy



Municipal Services



Packaging



Utilities



Warehousing and Distribution

IDEAL APPLICATIONS

- Automotive repairs and maintenance
- Intricate parts handling
- Mechanical and engineering
- Metal Stamping
- HVAC
- Public utility



TAA PRODUCTS

MADE IN USA

MATERIAL

- Glass Fiber
- HPPE
- Seamless knit
- Stainless steel

COATING

- PVC dots

GRIP

- Embossed

STANDARDS



SHOWA 910C



PACKAGING

- 12 Pair per polybag
- 72 Polybags per case
- 144 Gloves per case



SIZES

- XS
- S
- M
- L
- XL
- XXL

COLOUR



- white w/white dots



[USER INSTRUCTIONS

Do not use where there are chemical, electrical, thermal or entanglement risks. Wash at 40°C max. Performance levels as per standard EN388 retained after 3 washes, subject to variations linked to actual usage conditions. The performance levels apply to the coated surface only. Store in a dry place, away from the light.

[DISCLAIMER

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

Get in touch

SHOWA USA | 579 Edison Street - Menlo, GA 30731, USA

USA@SHOWAgroup.com

© SHOWA Group 2018 | All rights reserved