







M-10261



NOTE

1. DIMENSIONS IN INCHES [MILLIMETERS].
2. SUPPLIED ASSEMBLED WITH:
 - (1) .47"-32 THD. KNURLED NUT (BRASS, BLACK OXIDE).
 - (1) .47"-32 THD. HEX NUT (BRASS,NICKEL PLATE).

CATALOG NO. M11LTR

[illegible]

1	RELEASED PER DCN13301 GPK	JPP	10/20/0
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
MARINE TOGGLE SWITCH
SPST ON/OFF LIGHTED TIP

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS $\pm 1/64$ DECIMALS $\pm .005$ ANGLES $\pm 2'$	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
	DR. BY GPK	APP. BY JPP
	TR. BY	SCALE 1 = 1
	CHK'D BY TCM	DATE 10/20/0

DIMENSION SHEET FOR CAL. NO.

REPAIRABLE ☐ NON-REPAIRABLE ☐

B	M-10261
---	---------

1