RACO TAYMAC BELL

FLEXIBLE METAL STRAIGHT SQUEEZE CONNECTORS

Straight Squeeze Connectors, Uninsulated Malleable Iron

N/A





Catalog #: 2102

APPLICATIONS

For use in dry locations to bond flexible metal conduit to a box or enclosure $N\!/\!A$

1/2 in.

1-33/64 in. 17/32 in. 1/2 in. - 14 NPS

.590 in. .855 - .910

1-5/8 in.

PRODUCT FEATURES

All malleable iron construction insures mechanical protection for the raceway Electro zinc plated for added corrosion protection UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation

CULUS

UL Listed E195969

GENERAL PRODUCT INFORMATION	
Trade Size:	

DRAWING DIMENSIONS

Dimension A: Dimension B: Thread Spec. B: Dimension C: Dimension D: Dimension E:

PACKAGING

Package Type: Ship Carton Qty.: Product UPC-A Labeled: Weight (Lbs. Per/C): Ship Carton Length (in.): Ship Carton Height (in.): Ship Carton Height (in.): Ctn Weight (Lbs.): UPC Number: I2of5: Carton 50 No 14.80 10.00 5.25 4.31 7.40 050169021026 50050169021021

