



Nitrile

Extended, durable protection

- Enhanced thickness in the palm and finger for added durability
- Extended length provides superior protection in high-risk conditions



Industries

- Automotive
- Food Processing
- Life Sciences
- Machinery and Equipment
- Metal fabrication
- Chemical
- Healthcare

Recommended For

- Inspection, selecting, checking parts
- Equipment repair and maintenance
- Packing of fillets and ground meat
- Equipment, maintenance and repair
- All food processing, applications that have food contact
- Animal care feeding and cleanup
- Inspection (picking, checking and marking)
- Loading and unloading rough parts or boxes
- Testing
- Maintenance
- Extra protection over the wrist and arm
- Higher-risk clinical applications
- Protection from Type I latex allergy in HCW's or patients



TECHNICAL DATA SHEET

PRODUCT INFORMATION

	Integra® EC N87
Material	Nitrile
Color	Blue
Glove Design	Chlorinated, Powder-Free, Fully Textured
Cuff	Beaded
Manufacturing/QMS Audit Standards	ISO 13485:2003
Regulatory/Standards Compliance	ASTM D6319, EN 420:2003 + A1:2009, FDA21 CFR 177-2600, US QSR/FDA 510(k) Medical Examination Grade
Packaging	50 gloves per dispenser; 10 dispensers per case; 500 gloves per case
Storage	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country of Origin	Malaysia
Available sizes	S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10), XXL (10.5 - 11)
Anti-static	Not Tested

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	295 / 11.6		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.20 / 7.8		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.23 / 9.1		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	23	≥ 14	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412

ORDERING INFORMATION

Size	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	N871	N872	N873	N874	N875

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia

Ansell PYC
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.