

These industrial nitrile gloves offer versatile chemical protection of 18 mil, performing across a diverse range of applications

- Combining ruggedness and chemical resistance, protects workers' hands exposed to a greater variety of chemical hazards
- High performance nitrile compound, providing an outstanding combination of chemical resistance and strength, for optimal results in wet or dry work environments
- The glove offers a far superior snag, puncture and abrasion protection, compared with rubber or neoprene gloves
- High levels of flexibility, comfort and dexterity

Industries

- Automotive
- Machinery and Equipment
- Chemical

Applications

- Handling rough machined metal parts
- Equipment repair & maintenance
- Painting or cleaning tools or robots
- Changing tools and dies
- Handling incoming goods
- Filling, blending and charging of raw materials
- Opening and draining pumps valves or lines
- Loading and unloading of process equipment
- Transferring liquids and solids between vessels and tanks and process equipment
- Supervision of running operation
- Handling outgoing goods: cans, vessels, bulkpack and cartons
- Testing
- Opening furnaces draining pumps valves or lines and crackers BTX process



Key Features

- Cotton flocking, reducing sweat for the wearer
- Sandpatch finish giving the glove a smooth surface that decreases
- Indirect costs, thanks to fewer rejects of fragile parts
- Fully reusable, with an unequaled abrasion resistance
- Provides superb comfort for the wearer
- Complies with FDA food handling requirements (21 CFR 177.2600)



Performance Standards



EN ISO 374-5:2016



VIRUS

EN ISO 374-1:2016 Type A



JKLOPT

EN 388



4101X

EN 388



4101

EN 374



EN 374



JKL

EN 374



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec [®] Solvex [®] 37-175	Cotton Flocking, Nitrile,	6, 7, 8, 9, 10, 11	330 mm/ 13 inches	Green	• 12/polybag; 12 polybags/case

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2019 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.