



MCR
SAFETY

BearKat

Safety Glasses

RX Option Series

Specification Sheet

PRODUCT DESCRIPTION:

The BearKat® Magnifier's well thought-out construction combines the best in safety, comfort, and affordability! Your vision is unobstructed by the frameless one-piece wraparound lens, which by its secure fit allows you maximum safety. Comfort is enhanced by the flexible temples and the non-slip temple sleeves are notched on the end to accept a clip-on breakaway cord! These magnifiers are available in a variety of diopter strengths so there is an option that is just right for you! Meets or exceeds ANSI Z87+ and CSA Z94.3.



FEATURES:

- 1.0, 1.5, 2.0, 2.5 Diopter available
- Single lens design with integral side shields for unobstructed view
- Non-Slip soft temple material
- Exclusive Duramass® scratch resistant coating
- Rugged polycarbonate lens filters 99.9% of harmful U.V. rays
- ANSI Z87+ and CSA Z94.3

TECHNICAL DATA FOR: BKH20

Series	BearKat	Scratch Resistant	Yes
Category	Safety Glasses	Magnifier	2.0
		Packaging	White Inner Box
Case Pack	144 pair	AS/NZS 1337.1	N/A
Case Dimensions	22.441 x 14.961 x 12.992	CE EN166	N/A
Case Weight	6.183 oz.	ANSI D3 SPLASH	N/A
Made In	Taiwan	ANSI D4 DUST	N/A
MIL - PRF - 31013	N/A	CAN/CSA Z94.3	Yes
ANSI Z87+	Yes		

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
BK010	Clear	Uncoated	No	90	N/A	Clear	Black



MCR
SAFETY

BearKat Safety Glasses

RX Option Series Specification Sheet

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
BK012	Gray	Uncoated	No	13	N/A	Gray	Black
BK110	Clear	Duramass Hard Coat	Yes	90	N/A	Clear	Black
BK110AF	Clear	Duramass Anti-Fog	Yes	90	N/A	Clear	Black
BK112	Gray	Duramass Hard Coat	Yes	13	N/A	Gray	Black
BK112AF	Gray	Duramass Anti-Fog	Yes	13	N/A	Gray	Black
BK113	Light Blue	Duramass Hard Coat	Yes	68	N/A	Light Blue	Black
BK114	Amber	Duramass Hard Coat	Yes	80	N/A	Amber	Black
BK116	Orange	Duramass Hard Coat	Yes	57	N/A	Orange	Black
BK117	Silver Mirror	Duramass Hard Coat	Yes	13	N/A	Smoke	Black
BK118	Blue Mirror	Duramass Hard Coat	Yes	13	N/A	Smoke	Black
BK119	I/O Clear Mirror	Duramass Hard Coat	Yes	36	N/A	Clear	Black
BKH10	Clear	Duramass Hard Coat	Yes	90	N/A	Clear	Black
BKH10G	Gray	Duramass Hard Coat	Yes	13	N/A	Gray	Black
BKH15	Clear	Duramass Hard Coat	Yes	90	N/A	Clear	Black
BKH15G	Gray	Duramass Hard Coat	Yes	13	N/A	Gray	Black
BKH20	Clear	Duramass Hard Coat	Yes	90	N/A	Clear	Black
BKH20G	Gray	Duramass Hard Coat	Yes	13	N/A	Gray	Black
BKH25	Clear	Duramass Hard Coat	Yes	90	N/A	Clear	Black
BKH25G	Gray	Duramass Hard Coat	Yes	13	N/A	Gray	Black

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved