

PC 621



HEAVY DUTY CLOTH DUCT TAPE

TYPICAL APPLICATIONS

- For demanding HVAC applications to hold, seal and seam sheet metal and flex duct, exhaust vents and preformed insulation
- Can also be used in industrial applications for holding, splicing, protecting and packaging

PRODUCT FEATURES

- Excellent tack, conformability and holding power
- Easy to unwind and tear
- Will not twist or curl during application

CONSTRUCTION

Overall Grade/Function: Heavy duty

Backing: Waterproof polyethylene film with a cloth carrier

Adhesive: Natural rubber

STANDARD WIDTH(S)

48 mm 72 mm

STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



BLACK
(BLK)



SILVER
(SIL)



SILVER PRINTED
(SPT)

PHYSICAL PROPERTIES STANDARD METRIC

Tensile Strength	27 lbs/in width	47.3 N/10 mm
Adhesion to Stainless Steel	62 oz/in width	6.79 N/10 mm
Thickness	11 mils	0.28 mm
Elongation	10%	10%
Service Temperature Range	50 F to 200 F	10 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

