

More power for tough cuts

PowerArc™ technology provides over 40% more power, especially during the toughest part of the cut.

PowerArc™

40%

MORE POWER

Extended tang

Open handle for maximum leverage

Stainless steel Micro-Tip® blades

Spring-assisted handle

PowerArc™

40%

MORE POWER

EASY ACTION™

SPRING ASSISTED HANDLE

INNOVATIVE DESIGN

FULL

LIFE TIME

WARRANTY

PowerArc™ technology features intelligently curved blades that alter the angle between blades to maximize your power.

Spring-assisted Easy Action™ handle prevents overextension and reduces hand fatigue.

Open top handle loop allows you to rotate your hand over the handle to apply more power.

Fiskars® Pro products are backed by a lifetime warranty.

JOBSITE TESTED

22_{GA}

CUT CAPACITY

REPLACEABLE BLADES