

Features and Benefits

Commercial Standard Hospital Grade ● GFCI Receptacles

- Fed. Spec UL Listed, Hospital Grade
- Green power indicator and red trip indicator
- Patented AUTOGUARD® self test technology
- Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple



GFRST82WNL



15A 125V
NEMA 5-15R
UL CSA
0.5 HP



20A 125V
NEMA 5-20R
UL CSA
1 HP

Hospital Grade ● GFCI Receptacles

Description	Rating	Color	Catalog Number	
Standard, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFRST82BK	GFRST83BK
		Brown	GFRST82	GFRST83
		Gray	GFRST82GY	GFRST83GY
		Ivory	GFRST82I	GFRST83I
		Light Almond	GFRST82LA	GFRST83LA
		Red	GFRST82R	GFRST83R
		White	GFRST82W	GFRST83W
Assembled in USA, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFRST82BKU	GFRST83BKU
		Brown	GFRST82U	GFRST83U
		Gray	GFRST82GYU	GFRST83GYU
		Ivory	GFRST82IU	GFRST83IU
		Light Almond	GFRST82LAU	GFRST83LAU
		Red	GFRST82RU	GFRST83RU
		White	GFRST82WU	GFRST83WU
Night Light Two LED Night Lights, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFRST82BKNL	GFRST83BKNL
		Brown	GFRST82NL	GFRST83NL
		Gray	GFRST82GYNL	GFRST83GYNL
		Ivory	GFRST82INL	GFRST83INL
		Light Almond	GFRST82LANL	GFRST83LANL
		Red	GFRST82RNL	GFRST83RNL
		White	GFRST82WNL	GFRST83WNL
Alarm, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFRST82BKB	GFRST83BKB
		Brown	GFRST82B	GFRST83B
		Gray	GFRST82GYB	GFRST83GYB
		Ivory	GFRST82IB	GFRST83IB
		Light Almond	GFRST82LAB	GFRST83LAB
		Red	GFRST82RB	GFRST83RB
		White	GFRST82WB	GFRST83WB
SNAPConnect®, Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFRST82SNAPBK	GFRST83SNAPBK
		Brown	GFRST82SNAP	GFRST83SNAP
		Gray	GFRST82SNAPGY	GFRST83SNAPGY
		Ivory	GFRST82SNAPI	GFRST83SNAPI
		Light Almond	GFRST82SNAPLA	GFRST83SNAPLA
		Red	GFRST82SNAPR	GFRST83SNAPR
		White	GFRST82SNAPW	GFRST83SNAPW



GFRST82R



GFRST83INL



GFRST83BKB



GFRST83SNAPGY

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles are furnished with a matching color thermoplastic wallplate, 20 amp feed-through capability. Requires pigtailed connector see page M-14.