



Cut



Medium Duty

Highly durable cut-resistant gloves, with strong blended fibers and reinforced thumb crotch

- **Heightened defenses:** HyFlex® 11-738 industrial gloves' INTERCEPT™ Cut Resistance Technology yarn, blended with Nylon®, Lycra® and strengthened fibers, provide both cut and heat protection
- **Advanced durability:** FORTIX™ Abrasion Resistance Technology delivers long-lasting durability
- **Targeted protection:** HyFlex® 11-738 safety gloves' reinforced thumb crotch results in 12x greater resilience than unreinforced competitor gloves
- **Elevated comfort:** Water-based polyurethane and nitrile coating improves grip, while enhancing comfort and dexterity
- **Approved skin-friendliness:** They also benefit from Oeko-Tex® certification for skin-friendliness
- **Contaminant-free:** HyFlex® 11-738 PPE gloves are silicone-, DMF- and solvent-free



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Automotive Aftermarket
- Utilities
- Warehousing

Applications

- Handling of sharp-edged objects, pre-assembling, cutting of small dry or lightly oiled parts and maintenance
- Handling of glass sheets, sharp edged objects
- Handling of metal sheets, cutting of dry, painted or galvanised pieces

Key Features

- INTERCEPT™ Cut Resistance and strong fibers: Robust cut protection
- FORTIX™ Abrasion Resistance: PPE gloves with heightened durability
- Reinforced thumb crotch: Targeted hand protection and resilience

Technologies



FORTIX™
Abrasion Resistance Technology



INTERCEPT™
Cut Resistance Technology

Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-738	Finishing: Palm Coated Coating Material: Water-Based polyurethane and nitrile Liner Material: Fiber glass, HPPE, Polyester, Spandex Cuff Style: Knitwrist	13	6, 7, 8, 9, 10, 11	225-275 mm; 8.85-10.82 inches	Black	• 12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306.
Col. Centro Sur, c.p. 76079
Queretaro, Gro. Mexico
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306.
Col. Centro Sur, c.p. 76079
Queretaro, Gro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.