



**MCR
SAFETY**

**9688
Flex Tuff
Dipped
Specification Sheet**

PRODUCT DESCRIPTION:

Our top selling FlexTuff® styles are manufactured on seamless knit liners that are flat dipped to reproduce the natural curved shape of the hand. As a result, workers benefit from less hand fatigue and greater productivity while performing detailed tasks to heavy duty jobs. The FlexTuff® II series offers many of the benefits of the original FlexTuff® at a lower cost. Our top selling FlexTuff® styles are manufactured on seamless knit liners that are flat dipped to reproduce the natural curved shape of the hand.

FEATURES:

- 10 Gauge Gray Cotton/Polyester Shell
- Gray Latex Dip on the Palm and Fingertips
- Improves Grip
- Excellent comfort and fit

APPLICATIONS:

Automotive Assembly, Farming, Landscaping, Material Handling, Carpentry



TECHNICAL DATA FOR: 9688

Series	Flex Tuff	EN 388 : CE Score - Abrasion	2
Material Group	Strings	EN 388 : CE Score - Cut	1
Product Type	Dipped	EN 388 : CE Score - Tear	4
Glove Size	Large	EN 388 : CE Score - Puncture	2
Gauge	10 Gauge		
Material	Cotton Polyester Blend		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

9688
Flex Tuff
Dipped
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9688L	Large	10.36	5.99	3.15	35.376 lb.	2.948
9688M	Medium	9.80	5.76	2.87	32.724 lb.	2.727
9688S	Small	9.29	5.60	2.76	26.616 lb.	2.218
9688XL	X - Large	10.79	6.14	3.23	38.028 lb.	3.169

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved