



**MCR
SAFETY**

9665 Memphis Dipped Specification Sheet

PRODUCT DESCRIPTION:

Economy PU coated Nylon provides good tactile sensitivity, dexterity, and abrasion resistance. They feature a 13 gauge Nylon shell with polyurethane palm and finger coating. These gloves come with color coded hem sizing and are individually poly bagged by the pair. Made without Silicone.

FEATURES:

- 13 Gauge White Nylon Shell
- Gray PU Coated Palm and Fingertips
- Individually poly bagged by the pair
- Color coded hem to identify sizes

APPLICATIONS:

Assembly Line Production, Automotive Assembly, Furniture industry, Janitorial , Landscaping, Mechanics



TECHNICAL DATA FOR: 9665

| | | | |
|-----------------------|----------|-------------------------------------|---|
| Series | Memphis | EN 388 : CE Score - Abrasion | 4 |
| Material Group | Strings | EN 388 : CE Score - Cut | 1 |
| Product Type | Dipped | EN 388 : CE Score - Tear | 3 |
| Glove Size | Large | EN 388 : CE Score - Puncture | 1 |
| Gauge | 13 Gauge | | |
| Material | Nylon | | |

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

9665
Memphis
Dipped
Specification Sheet



| Item No: | Size: | A: | B: | C: | Case Weight | UOM Weight |
|----------|-----------|-------|------|------|-------------|------------|
| 9665L | Large | 10.04 | 5.28 | 2.83 | 11.316 lb. | 0.943 |
| 9665M | Medium | 9.65 | 5.12 | 2.76 | 10.860 lb. | 0.905 |
| 9665S | Small | 9.29 | 4.48 | 2.68 | 9.828 lb. | 0.819 |
| 9665XL | X - Large | 10.43 | 5.44 | 2.95 | 12.180 lb. | 1.015 |
| 9665XS | X - Small | 8.89 | 4.48 | 2.56 | 9.000 lb. | 0.750 |
| 9665XXS | XX -Small | 8.85 | 4.20 | 2.55 | 8.604 lb. | 0.717 |

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved