



**MCR
SAFETY**

9786

Predalite

**Supported / Dipped gloves
Specification Sheet**

PRODUCT DESCRIPTION:

This nitrile coated option can hold up to those tough environments that you face each day. Abrasion, snag, and puncture resistance combined with a soft interlock lining makes this glove a safe option that you can comfortably wear for extended periods of time. Treated with Actifresh to help fight odor. The 9786 is fully coated with nitrile and features a PVC coated safety cuff.

FEATURES:

- Light Nitrile Palm Coated
- Interlock Lining
- PVC Safety Cuff
- CE Score 4121
- Treated with Actifresh®
- Component materials comply with all federal regulations for food contact

APPLICATIONS:

Food, Oil and Gas Industry, Carpentry, Construction, Landscaping



TECHNICAL DATA FOR: 9786

Series	Predalite
Material Group	Supported
Product Type	Supported / Dipped gloves
Glove Size	Large
Material	Nitrile
Grade	Premium
Lining	Interlock
Thumb Style	Straight

Overall Length	11 in.
EN 388 : CE Score - Abrasion	4
EN 388 : CE Score - Cut	1
EN 388 : CE Score - Tear	2
EN 388 : CE Score - Puncture	1
FDA Accepted Materials	FDA Compliant

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

9786

Predalite

Supported / Dipped gloves

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9786L	Large	10.826	5.827	N/A	39.444 lb.	3.287
9786M	Medium	10.433	5.433	N/A	33.900 lb.	2.825
9786S	Small	10.237	5.118	N/A	30.432 lb.	2.536
9786XL	X - Large	11.024	6.300	N/A	39.396 lb.	3.283

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved