



**MCR
SAFETY**

6702F

**Supported / Dipped gloves
Specification Sheet**

PRODUCT DESCRIPTION:

Frigid frozen fingers? No frickin' way, These foam-insulated gloves keep hands warm and dry. They are resistant to abrasions, oil, acids, chemicals and caustics.

FEATURES:

- Premium Foam Lined
- Double Dipped PVC
- Fluorescent Orange
- Smooth Finish
- Knit Wrist

APPLICATIONS:

Food, Cold storage applications, Fisheries, Transportation, Warehousing



TECHNICAL DATA FOR: 6702F

Material Group	Supported	Overall Length	11.5 in.
Product Type	Supported / Dipped gloves	EN 388 : CE Score - Abrasion	3
Glove Size	Large	EN 388 : CE Score - Cut	1
Material	PVC	EN 388 : CE Score - Tear	2
Grade	Premium	EN 388 : CE Score - Puncture	1
Insulated	Insulated		
Lining	Foam		
Thumb Style	Wing		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com


©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

6702F

Supported / Dipped gloves
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
6702F	Large	11.400	6.38	3.30	29.960 lb.	5.992

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved