

## 2000 COMFORT - Model 129

Superior breathable microporous laminate technology, Type 5/6 protection

Previously known as: MICROCHEM® by AlphaTec® 2000 COMFORT - Model 129

**Designed for workers in warm environments to provide an optimum balance between comfort and protection.**

- Protection - Hood, arms, legs and front torso in AlphaTec® 2000 fabric
- Comfortable to wear featuring moisture vapor permeable fabric (“breathable”) to help reduce the risk of heat stress
- Silicone free, critical in spray painting applications
- Anti-static, tested according to EN 1149-5

### Industries

- Automotive
- Life Sciences
- Food Processing
- Metal fabrication

### Applications

- Clean room cleaning and preparing
- Body painting including surface inspection
- Production line support & maintenance
- Cleaning of plant and machines
- Maintenance of plant and machines
- Crime Scene Investigation (CSI)
- Veterinary Services



# AlphaTec®

ADVANCED CHEMICAL PROTECTION

## 2000 COMFORT - Model 129

Superior breathable microporous laminate technology, Type 5/6 protection

Previously known as: MICROCHEM® by AlphaTec® 2000 COMFORT - Model 129

### PRODUCT INFORMATION

<b>Product Material</b>	Microporous Polyethylene Laminate nonwoven (hood, arms and legs) and Polypropylene nonwoven with anti-static treatment (back panel)
<b>Design Features</b>	3-piece hood, 2-way front zipper with re-sealable storm flap, finger loops. Elasticated hood, waist, wrists and ankles. Breathable SMS back panel.
<b>Seam Type</b>	Bound Seams
<b>Standards Overview</b>	CE CATEGORY III (Type 5, Type 6, EN 1073-2, EN 1149-5)
<b>Product Reference</b>	2000 COMFORT - Model 129
<b>Sizes</b>	S-6XL (02-10)
<b>Weight</b>	Microporous Polyethylene Laminate nonwoven 63 gsm Polypropylene nonwoven with anti-static treatment 48gsm

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306.  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2019 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

