

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-928

Dual protection from cuts and mechanical fluids



Cut

Ergonomic Protection



Medium Duty

## Strong protection for strong hands

- INTERCEPT™ Technology ANSI Cut Level 4 performance for the ultimate in cut resistance
- Double layer RIPEL™ nitrile coating keeps hands dry & comfortable when handling oily parts and tools
- Intermittent contact heat protection when handling hot parts up to 212 degrees Fahrenheit



### Industries

- Automotive
- Metal fabrication
- Machinery and Equipment
- Oil and gas

### Applications

- General maintenance
- Handling sharp or irregular metal pieces
- Handling of glass sheets, sharpedged objects
- Grinding
- Machining / Stamping / Cutting

#### Key Features

- Glass-free INTERCEPT liner provides increased cut protection
- Silicone and DMF free
- Grip performance for safe handling in dry to light oily applications
- Double dipped nitrile coating protects against oil and industrial fluid exposure while providing high durability and extended use life
- INTERCEPT Aramid Liner for increased cut performance
- Contact Heat Protection Level 1

#### Technologies



DMF free



Fibre glass free



#### Performance Standards & Regulatory Compliance

##### REACH Compliant



4X32D



X1XXXX

CE 0086



ABR



CUT

#### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-928	<b>Finishing:</b> ¾ Dipped <b>Coating Material:</b> Nitrile <b>Liner Material:</b> Ansell INTERCEPT™ Technology, Aramid <b>Cuff Style:</b> Knitwrist	15	7, 8, 9, 10, 11	236-265mm/9.3-10.4 inches	Black	• 12 pairs per polybag / 12 polybags per carton

#### For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

##### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

##### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

##### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

##### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jaijan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

##### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

##### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:  
[www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.