



# Rapid Start T12

## F40DX ALTO 30PK

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

### Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Base	G13 [ Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	20000 h
Life with 3 Hour Per Day Use	7 a
Features	ALTO® (ALTO)
System Description	Rapid Start (RS)

Light Technical	
Color Code	57
Initial lumen (Nom)	2325 lm
Color Designation	Daylight Deluxe
Design Mean Lumens	2025 lm
Correlated Color Temperature (Nom)	6500 K
Color Rendering Index (Nom)	90

Operating and Electrical	
Power (Rated) (Nom)	40 W

Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	48
Bulb Shape	T12 [ T12 (T12)]

Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	4.4 mg


Product Data	
Order product name	F40DX ALTO 30PK
EAN/UPC - Product	046677273590
Order code	273599
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927888005709
Net Weight (Piece)	0.230 kg

## Rapid Start T12

### Dimensional drawing

#### Product

F40DX ALTO 30PK



F40T12/57 48 ALTO

