



High CRI T12

F40T12/C50Supreme/ALTO 30pk

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Nominal Length (Inch)	
Base	G13 [Medium Bi-Pin Fluorescent]		48
Life 3-Hr Start [Hrs]	20000 h	Bulb Shape	T12 [T12 (T12)]
Life 12-Hr Start [Hrs]	24000 h	Approval and Application	
Features	ALTO® (ALTO)	Energy Saving Product	Energy Saving
Light Technical		Mercury (Hg) Content (Nom)	4.4 mg
Initial lumen (Nom)	2545 lm	Product Data	
Color Designation	C50 Supreme	Order product name	F40T12/C50Supreme/ALTO 30pk
Design Mean Lumens	2160 lm	EAN/UPC - Product	046677423896
Correlated Color Temperature (Nom)	5000 K	Order code	423897
Color Rendering Index (Nom)	90	Numerator - Quantity Per Pack	1
Operating and Electrical		Numerator - Packs per outer box	30
Power (Rated) (Nom)	40 W	Material Nr. (12NC)	927888000213
Mechanical and Housing		Net Weight (Piece)	0.230 kg
Cap-Base Information	Green Base		

High CRI T12

Dimensional drawing

Product

F40T12/C50Supreme/ALTO 30pk



F40T12 C50 Supreme ALTO®

