

## Mega Textured nitrile gloves that offer a comfortable, confident grip when handling wet, oily, or fatty foods and objects

- Feature a Mega Texture surface for secure grip
- Have a generous fit for comfortable use with a cut-protective or thermal under gloves
- The robust 0.20 mm/8 mil thickness resists tearing, for product protection
- Compliant with US Food Contact and EU Food Migration Regulations



### Industries

- Food Processing
- Janitorial / Sanitation

### Recommended For

- Packaging and labeling
- Food processing and handling
- Cold storage
- Deboning, carving
- Handling of frozen foods
- Janitorial, clean up and maintenance
- Processing meat, vegetables and dairy sanitation
- Secondary food processing



## TECHNICAL DATA SHEET

### PRODUCT INFORMATION

	<b>93-287</b>
<b>Material</b>	Nitrile
<b>Color</b>	Green
<b>Glove Design</b>	Powder-Free, Chlorinated, Raised Diamond Grip Pattern
<b>Cuff</b>	Beaded
<b>Regulatory/Standards Compliance</b>	ASTM D6319, EC 2023/2006, EC 1935/2004, EN ISO 374-1:2016, EN 420:2003 + A1:2009, EN 420:2003 + A1:2009, EN ISO 374-5:2016, FDA21 CFR 177-2600, ISO 13485, ISO 9001
<b>Packaging</b>	50 gloves per dispenser; 10 dispensers per case; 500 gloves per case; 2XL and 3XL: 44 gloves per dispenser; 440 gloves per case
<b>Storage</b>	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
<b>Country of Origin</b>	Malaysia
<b>User Needs Segment</b>	High Risk
<b>Available sizes</b>	S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10), XXL (10.5 - 11), XXXL (11.5 - 12)
<b>Anti-static</b>	No

### PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	300 / 11.8		ASTM D3767, EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151, EN 374-2
Palm Thickness (mm/mils)	0.20 / 7.9		ASTM D3767, EN 420
Finger Thickness (mm/mils)	0.22 / 8.7		ASTM D3767, EN 420
	<b>BEFORE AGING</b>	<b>AFTER AGING</b>	
Ultimate Tensile Strength (MPa)	28	25	ASTM D412 & D573
Elongation at Break (%)	450	420	ASTM D412
Force at break (N)	10	6	EN 455-2

### ORDERING INFORMATION

Size	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)	XXXL (11.5 - 12)
<b>Product Code</b>	93287070	93287080	93287090	93287100	93287110	93287120

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
T: +603 8310 6688  
F: +603 8310 6699

#### North America Region

Ansell Healthcare Products LLC  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

#### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Russia

Ansell PYC  
Ten. +7 495 258 13 16

### Performance Standards and Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.