



MCR
SAFETY

6700F

Supported / Dipped gloves Specification Sheet

PRODUCT DESCRIPTION:

Frigid frozen fingers? No frickin' way, These foam-insulated gloves keep hands warm and dry. They are resistant to abrasions, oil, acids, chemicals and caustics.

FEATURES:

- Premium Foam Lined
- Double Dipped PVC
- Fluorescent Orange
- Sandy Finish
- Knit Wrist

APPLICATIONS:

Cold storage applications, Fisheries, Transportation, Warehousing, Agriculture, Farming, Material Handling



TECHNICAL DATA FOR: 6700F

Material Group	Supported
Product Type	Supported / Dipped gloves
Glove Size	Large
Material	PVC
Grade	Premium
Insulated	Insulated
Lining	Foam
Thumb Style	Wing


Overall Length	11.5 in.
EN 388 : CE Score - Abrasion	4
EN 388 : CE Score - Cut	1
EN 388 : CE Score - Tear	1
EN 388 : CE Score - Puncture	2



MCR
SAFETY

6700F

Supported / Dipped gloves Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
6700F	Large	11.024	7.126	3.000	18.348 lb.	6.116

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved