



## Item # IM-21

Non-Sparking, Non-Magnetic, Corrosion-Resistant  
1000V Rated (Adjustable Wrenches are not 1000V Rated)

### Set Includes:

- **Adjustable Combination Pliers, 8"**: IP-31
- **Linemans'/Side Cutting Pliers, 8-1/2"**: IP-35
- **Groove Joint Pliers**: IP-39
- **#2 Phillips Screwdriver**: IS-1099
- **Standard Screwdriver, 5/16" Tip**: IS-49
- **Adjustable Wrench, 8"**: IW-71
- **Choice of 2 Single Box End Wrenches, 12-Point - 7/16", 1/2" or 9/16**: IWSB-7/16, IWSB-1/2 or IWSB-9/16
- **Toothbrush Style Scratch Brush with Wooden Handle**: TB-10
- **Tool Box**: M-49-BOX



### Specifications

-

length (mm)

405

width (mm)

235

height (mm)

205

<b>Wt (g)</b>	3400
<b>length (in)</b>	16
<b>width (in)</b>	9-1/4
<b>height (in)</b>	8
<b>Wt (lbs)</b>	7.50