

# Locking Devices

## 15 Amp Locking Receptacles

15A 125V, 250V and 277V Locking Devices, 2-Pole 3-Wire Grounding Inches (mm)

**TECH-SPEC®**



Rating	Description	Back and Side Wired					Mounted on a 4" (101.6) Round Cover
		Duplex Receptacle Reinforced Thermoplastic Polyester (RTP)	Nylon	Single Receptacle Panel Mount Mounting Hole Center		4711BRY	
				1.94" (49.3)	1.75" (44.5)		
NEMA L5-15, 15A 125V Plug  Connector	Black Brown Ivory Isolated Ground Orange Corrosion-Resistant Yellow	— <b>4700DR</b> <b>4700DRI</b> <b>4700DRIG</b> <b>4700DRCR</b>	<b>4710</b> — — <b>4710IG</b> <b>4710CR</b>	<b>4712BRY</b> — — — —	<b>4713BRY</b> — — — —	<b>4711BRY</b> — — — —	
NEMA L6-15, 15A 250V Plug  Connector	Black Brown Isolated Ground Orange	— <b>70615DR</b> <b>70615DRIG</b>	<b>70615FR</b> — <b>70615IG</b>	<b>7061594</b> — —	<b>7061575</b> — —	— — —	
NEMA L7-15, 15A 277V AC Plug  Connector	Black Brown	— <b>4750DR</b>	<b>4760</b> —	— —	— —	<b>4761</b> —	

Note: See Section D for more information on isolated ground devices and Section J for more information on corrosion-resistant devices.

## Receptacle Accessories



Single Receptacle Wallplate		Duplex Receptacle Wallplate		Weatherproof Covers		
Stainless Steel	Nylon	Stainless Steel	Nylon	Zinc Die Cast	Zinc Die Cast	Thermoplastic
<b>SS7</b>	<b>NP7BK</b>	<b>SS8</b>	<b>NP8BK</b>	<b>RW51550</b>	<b>RW51470</b>	<b>RW57300</b>

Note: See Section Q for additional information on wallplates and weatherproof covers.

## Product Dimensions Inches (mm)

Receptacle	
Duplex	Single
A 3.28" (83.3)	3.28" (83.3)
B 2.74" (69.6)	2.38" (60.5)
C 1.70" (43.2)	1.38" (35.1)
D 1.17" (29.7)	1.41" (35.8)
E 0.93" (23.6)	1.37" (37.8)
F —	1.01" (25.7)

  

Panel Mounting	
A 2.38" (60.5)	
B 1.75" (44.5) or 1.94" (49.3)	
C 1.38" (35.1)	
D 1.41" (35.8)	
E 1.09" (27.7)	
F 0.33" (8.4)	

