



# Straight Blade Devices

## Commercial Grade Duplex Tamper-Resistant Receptacles



### 15A and 20A 125V Self-Grounding Tamper-Resistant Receptacles



Wiring		Side Wired		Back and Side Wired	
Rating	Color	Standard	Standard*	Decorator	Decorator, Nightlight
NEMA 5-15, 15A 125V 	Black	<b>CRS15BLKTR</b>	<b>CBRS15BLKTR</b>	<b>DRS15BLKTR</b>	—
	Brown	<b>CRS15TR</b>	<b>CBRS15TR</b>	<b>DRS15TR</b>	—
	Gray	<b>CRS15GRYTR</b>	<b>CBRS15GRYTR</b>	<b>DRS15GRYTR</b>	—
	Ivory	<b>CRS15ITR</b>	<b>CBRS15ITR</b>	<b>DRS15ITR</b>	<b>DRS15NLI</b>
	Light Almond	<b>CRS15LATR</b>	<b>CBRS15LATR</b>	<b>DRS15LATR</b>	<b>DRS15NLLA</b>
White	<b>CRS15WTR</b>	<b>CBRS15WTR</b>	<b>DRS15WTR</b>	<b>DRS15NLW</b>	
NEMA 5-20, 20A 125V 	Black	<b>CRS20BLKTR</b>	<b>CBRS20BLKTR</b>	<b>DRS20BLKTR</b>	—
	Brown	<b>CRS20TR</b>	<b>CBRS20TR</b>	<b>DRS20TR</b>	—
	Gray	<b>CRS20GRYTR</b>	<b>CBRS20GRYTR</b>	<b>DRS20GRYTR</b>	—
	Ivory	<b>CRS20ITR</b>	<b>CBRS20ITR</b>	<b>DRS20ITR</b>	—
	Light Almond	<b>CRS20LATR</b>	<b>CBRS20LATR</b>	<b>DRS20LATR</b>	—
White	<b>CRS20WTR</b>	<b>CBRS20WTR</b>	<b>DRS20WTR</b>	—	



Note: See page R-6 for tamper-resistant and weather resistant descriptions.  
See page A-11 for dimensional art.  
\*Fed. Spec. Listed.

### 15A and 20A 125V Self-Grounding Weather Resistant and Tamper-Resistant Receptacles



### 15A and 20A 125V Self-Grounding Weather Resistant Receptacles



Wiring		Back and Side Wired	
Rating	Color	Standard	Decorator
NEMA 5-15, 15A 125V 	Black	<b>CBRS15BLKWTR</b>	<b>DRS15BLKWTR</b>
	Brown	<b>CBRS15WRTR</b>	<b>DRS15WRTR</b>
	Gray	<b>CBRS15GRYWTR</b>	<b>DRS15GRYWTR</b>
	Ivory	<b>CBRS15IWRTR</b>	<b>DRS15IWRTR</b>
	Light Almond	<b>CBRS15LAWTR</b>	<b>DRS15LAWTR</b>
White	<b>CBRS15WWTR</b>	<b>DRS15WWTR</b>	
NEMA 5-20, 20A 125V 	Black	<b>CBRS20BLKWTR</b>	<b>DRS20BLKWTR</b>
	Brown	<b>CBRS20WRTR</b>	<b>DRS20WRTR</b>
	Gray	<b>CBRS20GRYWTR</b>	<b>DRS20GRYWTR</b>
	Ivory	<b>CBRS20IWRTR</b>	<b>DRS20IWRTR</b>
	Light Almond	<b>CBRS20LAWTR</b>	<b>DRS20LAWTR</b>
White	<b>CBRS20WWTR</b>	<b>DRS20WWTR</b>	

Note: See page R-6 for tamper-resistant and weather resistant descriptions.  
See page A-11 for dimensional art.

Back and Side Wired	
Color	Standard*
Black	<b>CBRS15BLKWTR</b>
Brown	<b>CBRS15WR</b>
Gray	<b>CBRS15GRYWTR</b>
Ivory	<b>CBRS15IWR</b>
Light Almond	<b>CBRS15LAWR</b>
White	<b>CBRS15WWR</b>
Black	<b>CBRS20BLKWTR</b>
Brown	<b>CBRS20WR</b>
Gray	<b>CBRS20GRYWTR</b>
Ivory	<b>CBRS20IWR</b>
Light Almond	<b>CBRS20LAWR</b>
White	<b>CBRS20WWR</b>

Note: \*Fed. Spec. Listed.