Twist-Lock® Devices 20A, 125/250V AC, 3 Pole, 4 Wire Grounding Watertight Safety-Shroud® Receptacle

HUBBELL

Features

- High impact, thermoplastic housing for heavy-duty industrial environments
- Alignment arrows with lock and unlock symbols provide a visual indication that devices are properly connected
- Catalog number and color coded voltage rating are visible even when in use

Ordering Information

Description Device Color UPC Catalog Number PBT housing and Gray 783585231266 HBL2410SW flange.

Listings

Listed to UL 498
Fed.Spec. W-C-596
Certified to CSA C22.2 No.42
UL Listed, CSA Certified to Type 4, 4X and Type 12

Specifications

Housing / Cover Gray RPT
Terminal Retainer Clear polycarbonate
Body Contact Carrier Natural (white) nylon
Drive Screws Steel, zinc plated

Contacts Brass

Lift-Cover Spring & Pin Stainless Steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #16 AWG - #8 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498


Environmental

Flammability V2 or better per UL94/CSA 22.2 No.0.17

Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)





Accessories

Watertight Safety Shroud Plug
Non-Metallic Backbox
2-Gang Weatherproof Box
Adapter Plate
Mechanical Interlock
HBL2411SW
BB2030N
HBL2030AP
HBL2030AP

Resources

Customer Use Drawing eCatalog

